

Pneumatic dispenser Dispenser 200 ETC

POLY DISPENSING SYSTEMS

122, Chemin de la Cavée - 78630 Orgeval • contact@polydispensing.com • Tel : 01.39.62.40.92 www.polydispensing.com

DATA SHEET

Dispenser 200 ETC

PDS 200ETC

Specifications

- Teach fonction
- Time and operating modes display
- 39 programs
- End cycle drawback, clean cut
- Foot switch
- Repeatable dispense
- Manual mode
- Cycle mode
- Timer mode
- Output signal


Electro pneumatic dispensers applicators are recommanded for the constant deposit of liquid, fluid or pasty products of all kinds, in a repetitive and calibrated way.

They benefit from an accurate setting of the pressure to obtain a constant flow of the product and a setting of the deposit time to a thousandth of a second.

The application, in a syringe, of a constant pressure set on the dispenser during a given time (numerical value settled on the dispenser) allows to dispense a quantity of repeatable material, on simple impulse of a foot pedal or a finger switch.

The vacuum setting allows to suck back the excess of material when the dispense is finished to avoid a drop when moving up the syringe.

200ETC dispensers benefit from an accurate setting of the time/pressure to obtain a constant debit of the product.



Dispenser 200 ETC

PDS 200ETC

Operating modes :

- Manual mode : enables dispenses related to pressure. By pressing on the pedal, the cycle starts and continues until the pressure on the pedal is released.
- Cycle mode : enables scheduled dispenses at set time. It is indeed a succession of dispenses.
- Timer mode : allows time/pressure dispenses. Pressing on the foot pedal starts the cycle which is carried out as per set parameters and regardless how long the pressure is operated on the foot pedal.

Material	Industrial metallic box
Screen	Digital
Dimensions	26 x 16 x 6. 5 cm
Weight	1.7kg
Monitoring	Foot pedal or finger switch
Air inlet	0-7 bars
AC power supply	90 - 120 ou 220 VAC
Speed	Over 600 cycles / minute

Applications : Points/Cords/ Filling Warranty : 2 years

- Dispense of all kind of fluids
- Release with foot pedal or figer switch
- Vacuum setting
- Syringes 3cc, 5cc, 10cc, 30cc et 55cc
- Industrial syringes, inert plastic, certified «silicone-free»

Dispensing consumables

For accurate dosing

Syringes : 5 different sizes

- Extra smooth sides
- A consistent and precise dispense, thanks to the perfect adjustement of the piston and the syringe.
- Batch and packing identification
- Clear, amber and opaque black for UV sensitive products

Pistons

- Designated for constant wipe
- Wasting avoided with efficient scrapping oh the sides of syringes
- Various models adapted to the products

Dispensing tips

- Luer-Lock fixation technology ensuring a secure connection of the needle to the syringe
- Wide selection of lenght, material and diameters

Poly Dispensing Systems



FRANCE - NORTH AFRICA Poly Dispensing Systems 122, Chemin de la Cavée 78630 Orgeval FRANCE 🕿 + 33 (0)1 39 62 40 92 🖹 + 33 (0)1 39 62 40 94 www.polydispensing.com SUISSE John P. Kummer AG Riedstr. 1 6330 Cham Suisse 🕿 +41 41 748 10 80 🖹 +41 41 748 10 89 www.jpkummer.com **BELGIQUE - HOLLANDE** LUXEMBOURG Gentec Benelux Rue de L'Industrie, 12 B-1400 Nivelles BELGIQUE **(*** +32 2 351 1800 - +32 2 351 1962 www.gentec-benelux.com

PDS S.A.S is a french company that commercializes a wide range of dosage equipments, proven and effective.

Distributed in over 20 countries around the world, these equipements provide tailored solutions to many users in order to improve technically their manufacturing and reduce their productions costs.

Our collaborators and sales engineers have strong technical competences. They are able to answer your questions and offer you, after analysis, the right solution for your particular need.

- NON CONTRACTUAL DOCUMENT -

POLY DISPENSING SYSTEMS

122, Chemin de la Cavée - 78630 Orgeval • contact@polydispensing.com • Tel : 01.39.62.40.92 www.polydispensing.com